












GAMAS ENCASTRE ZENIT R15 / RS15  
INSET RANGES ZENIT R15 / RS15



|                                                                                                                  |                                                                                                                     |      |     |                                                                                     |     |     |    |
|------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|------|-----|-------------------------------------------------------------------------------------|-----|-----|----|
|                                |                                  |      |     |  |     |     |    |
|                                                                                                                  |                                                                                                                     |      |     |                                                                                     |     |     |    |
|                                                                                                                  | A                                                                                                                   | B    | R   | C                                                                                   | D   | R1  |    |
|                                                                                                                  |  ZENIT R15 / RS15 1C / 1B          | 600  | 520 | 5                                                                                   | 584 | 504 | 10 |
|                                                                                                                  |  ZENIT R15 / RS15 1C 1E / 1B 1D 78 | 780  | 520 | 5                                                                                   | 764 | 504 | 10 |
|                                                                                                                  |  ZENIT R15 / RS15 1C 1E / 1B 1D 86 | 860  | 520 | 5                                                                                   | 844 | 504 | 10 |
|                                                                                                                  |  ZENIT R15 / RS15 2C / 2B 86       | 860  | 520 | 5                                                                                   | 844 | 504 | 10 |
|                                                                                                                  |  ZENIT R15 / RS15 1½C 1E / 1½B 1D  | 1000 | 520 | 5                                                                                   | 984 | 504 | 10 |
|  ZENIT R15 / RS15 2C 1E / 2B 1D | 1160                                                                                                                | 520  | 5   | 1144                                                                                | 504 | 10  |    |

